

31711

UST Broom, 400 mm, Soft, Pink



This ULTRA SAFE TECHNOLOGY (UST) Broom comes with angled Filament Security Units for effective sweeping of dry particles in high-risk areas. All UST brushes feature a unique bristle system that minimises the risk of contamination and bristle loss.

Technical Data

Item Number	31711
Visible bristle length	54 mm
Material	Polyester Glass reinforced Polypropylene
Complies with (EC) 1935/2004 on food contact materials ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates	No
Is Halal compliant	Yes
Patent Pend. No.	PA201270087, PA201270088
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	480 Pcs.
Quantity Per Layer (Pallet)	1 Pcs.
Box Length	410 mm
Box Width	290 mm
Box Height	210 mm
Length/Depth	400 mm
Width	50 mm
Height	95 mm
Gross Weight	0,44 kg
Net Weight	0,41 kg
Cubik metre	0,0019 M3
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. drying temperature	100 °C
Min. usage temperature ³	-20 °C
Max. pH-value in Usage Concentration	10,5 pH
Min. pH-value in usage concentration	2 pH
Recycling Symbol "7", Miscellaneous Plastics	Yes
GTIN-13 Number	5705020317118
GTIN-14 Number (Box quantity)	15705020317115
Commodity Code	96039099

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact
3. Do not store the product below 0° Celsius.