

Product data sheet

Specifications

Repacked, mounting box, Mureva Styl, 3 gangs, horizontal, anthracite



MUR37713W



This repacked option saves 0.717 over the standard condition

Main

Range of product	Mureva Styl
Product or component type	Mounting box
Range compatibility	Mureva Styl enclosure
Colour tint	Anthracite (RAL 7016)

Complementary

Device mounting	Surface
cable entry	Easy valve access
Condition of use	Indoor/outdoor
Material	SEBS PP (polypropylene)
Distance between centers	71 mm
Length	218 mm
Height	54 mm
Width	76 mm
Depth	54 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Quality labels	NF AENOR
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.600 cm
Package 1 Width	5.400 cm
Package 1 Length	21.800 cm
Package 1 Weight	174.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	2
Package 2 Height	8.000 cm
Package 2 Width	16.000 cm
Package 2 Length	39.500 cm
Package 2 Weight	441.000 g
Unit Type of Package 3	S04
Number of Units in Package 3	12
Package 3 Height	30 cm
Package 3 Width	40 cm
Package 3 Length	60 cm
Package 3 Weight	3.430 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.7 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

2c66ee7f-b39d-425f-a4af-fd0972454bc0

EU RoHS Directive

[Compliant](#)

REACH Regulation

[Free of Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No