

Han 16HP HBM with center screws



Image is for illustration purposes only. Please refer to product description.

Part number	29 39 016 0348
Specification	Han 16HP HBM with center screws
HARTING eCatalogue	https://harting.com/29390160348

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HP
Type of hood/housing	Bulkhead mounted housing

Version

Size	16 B
Locking type	Screw locking
Field of application	Hoods/housings for rough environments

Technical characteristics

Tightening torque	1 Nm Fixing screws M4
Tightening torque (screw locking)	3 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP68

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (seal)	NBR
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
Approvals	CE

Commercial data

Packaging size	1
Net weight	160.75 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140182226
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466