





1. 0.00013 [.000005] GOLD OVER 0.00127 [.000050] MIN NICKEL ALL OVER AND 0.00076 [.000030] MIN GOLD ON CONTACT AREA.
2. WIRE RANGE: 0.2-0.9mm² (24-18 AWG).
INSULATION RANGE: 2.79 [.110] DIA MAX.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± -		DR 11-2-92 K. SALMON CHK 11-2-92 R. SWING APPD 11-20-92 E. BEILES		AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL 0.33 [.013] BRASS		APPD - PRODUCT SPEC -		NAME RECEPTACLE, SL-156, LOOSE PIECE	
FINISH SEE TABLE		APPLICATION SPEC - WEIGHT -		SIZE C	CAGE CODE 00779
				DRAWING NO C-770258	
				SCALE 5:1	SHEET 1 OF 1

CUSTOMER DRAWING