

C376 - Athens Hi-Vis Mesh Executive Vest

Collection: MeshAir™

Range: High Visibility

Shell Fabric: MeshAir: 100% Polyester Mesh, 150g

Inner Pack: 10

Outer Carton: 60

Product information

Advanced MeshAir technology ensures excellent airflow keeping the wearer cool at all times. MeshAir fabric is also fully compliant with EN ISO 20471. This vest incorporates classic executive features including multiple pockets, ID holder, radio loop and zipped front for easy access.

MeshAir™

Portwest MeshAir™ fabric is lightweight and fully breathable making it ideal for working in warmer conditions. The open mesh fabric uses an advanced open knit construction which provides full airflow around the body and excellent ventilation. MeshAir fabric is fully tested and certified to EN ISO 20471.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 2

RIS 3279 TOM Issue 2 (Orange Only)



Features

- Cooling mesh fabric for increased breathability
- Front zip opening for easy access
- Dual ID holder allows use of both portrait and landscape ID card display
- D-ring for keys or ID cards
- Two lower patch pockets
- 7 pockets for ample storage
- Radio loop for easy clipping of a radio
- ID card holder for ID card display
- Phone and pen holder pocket
- Certified to EN ISO 20471 after 25x washes
- CE certified

C376 - Athens Hi-Vis Mesh Executive Vest
Commodity Code: 6110309100

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/11219-03/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/18402-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
C376ORRXS	Orange	43.0	28.0	48.0	0.2500	0.0578	5036108303397	15036108792419
C376ORRS	Orange	43.0	28.0	48.0	0.2560	0.0578	5036108285631	15036108775788
C376ORRM	Orange	43.0	28.0	48.0	0.2620	0.0578	5036108285624	15036108775771
C376ORRL	Orange	43.0	28.0	48.0	0.2680	0.0578	5036108285617	15036108775764
C376ORRXL	Orange	43.0	28.0	48.0	0.2810	0.0578	5036108285648	15036108775795
C376ORRXXL	Orange	43.0	28.0	48.0	0.2960	0.0578	5036108285655	15036108775801
C376ORRXXXL	Orange	43.0	28.0	48.0	0.3040	0.0578	5036108285662	15036108775818
C376ORR4XL	Orange	58.0	38.0	30.0	0.9990	0.0661	5036108510474	15036108995179
C376ORR5XL	Orange	58.0	38.0	30.0	0.9990	0.0661	5036108510481	15036108995186