



95-16

E0845078

Cable Lug KRF, 95mm², M16



Product Properties:

| | |
|----------------------------------|----------------------------------|
| Suitable for Class 5 conductor | Yes |
| Suitable for Class 6 conductor | Yes |
| Insulated | No |
| Max. current (I _{max}) | 288 A |
| Number of mounting holes | 1 . |
| Flange shape | Ring shape |
| Colour insulation | Other |
| Slender flange model | No |
| With sight-hole | Yes |
| Conductor category | Several |
| Max Temp | 150 °C |
| Surface protection | Tinned |
| Material | Copper |
| Connecting angle | 180° (horizontal) |
| Series | KRF/KSF (10-500mm ²) |

Dimensions:

| | |
|----|--------|
| HS | 17 mm |
| ID | 15 mm |
| OD | 20 mm |
| T | 4.8 mm |
| L | 69 mm |

| | |
|-------------------------|---------------------|
| N | 23 mm |
| W | 29 mm |
| MOQ | 50 . |
| Unit | pcs |
| Bolt dimension (metric) | 16 . |
| Nominal cross section | 95 mm ² |
| Series | KRF/KSF (10-500mm2) |

Approvals:

| | |
|----------------------------|-----|
| Approved according to CE | Yes |
| Approved according to UKCA | Ja |
| Approved according to DNV | Yes |

Compliance:

| | |
|-------------------|-------------------------------|
| Conflict Minerals | Contain "Tin" |
| Extended Minerals | Contain "Copper" |
| PFAS | No PFAS |
| REACH | No SVHC (Latest. 05 Nov 2025) |
| RoHS | RoHS 3 (2015/863) |
| SCIP | Not Applicable |

Other information:

| | |
|--------------------|---|
| ETIM-Class | EC001051 - Tube cable lug for copper conductors |
| ETIM-Release | 9.0 |
| Trademark | NEMIQ |
| Product Group | Cable lugs |
| Search Description | EFO2024V |
| Alternative SKU | 95-16 |
| E-no | E0845078 |

Logistic information:

| | |
|-------------------|--|
| Barcode | 733117612194 |
| Country of origin | CN |
| E-no | E0845078 |
| Item status | Stock item, normally in stock with reservation for in between sales. |
| MOQ | 50 . |
| Stock code | 95-16 |
| Taric code | 85369010 |
| Unit | pcs |

