

Datasheet

DIN Connector Socket

RS Stock number 811-8229



Specifications:

Connection Type:	3Pole + Earth
Voltage:	250V AC
Approvals:	N.A.
Standard:	N.A.
Mounting:	Screw-type
Type:	MEM -Socket (Micro DIN Connector) – Non-illuminated
Socket Type:	Type C
Mounting:	M3 Screw
Material For Rubber Gasket:	Nitril / Silicon
Material Body:	Nylon-6 GF
Gland Size:	PG-7
Body Colours:	Black / Grey
Contact Resistance (Initial):	20 m Ohms max.
Current Carrying Parts:	Copper Alloy, Tin plated
Permissible Temp. With/Without Load:	0°C to 90°C
Rating:	6A, 250VAC
Terminals:	Screw-type
H. V. Breakdown Test:	2 KV AC For 1 Minute.
Insulation Resistance:	100 M Ohms min.

Unit mm

BASIC DIMENSIONS

