

Part Number:1202510019

Status:Active

Overview:

Description:MPIS Ultra-Lock (M12) Passive Junction Box, Top-Mount, 4 Ports / 4 Poles, No LEDs, 5.0m Length, Single I/O Per Port

一般	
IP Rating	IP67
概要	ultralock_connection_system
製品名	Ultra-Lock (M12)
UPC	193264489527
機械的性能/材質	
Bus I/O	Ultra-Lock (M12)
Cable Connector Orientation	ストレート
ケーブル長	5.0m
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	Pigtail
Keyway	シングル
LED Indicator	無
Material - Cable Jacket	TPU
Material - Housing	PBT
材質 - 金属部	黄銅
材質 - 嵌合部メッキ	金
Net Weight	542.000/g
実装形態	Top-Mount
Poles	4
Poles (wired)	4
ポート	4
使用温度範囲	-25° C to +85° C
ケーブル種別	TPE
Wiring Configuration	Single I/O per Port
電気的性能	
最大定格電流	3.0A per port, 9.0A per module
Functional Wiring	Parallel
最大定格電圧	10-30V DC
参考情報	
Engineering Number	BKB4000-FBW-05
図面・仕様書情報	
製品図面	1202510019-000

EU ELV

Compliant with Exemption 3

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Compliant with Exemption 3

RoHS Phthalates

Not Contained

Search Parts in this Series

120119 Series