

Datasheet

Stock No: 811-4403

RS Pro 5 Core Unscreened White 3185Y Power Cable



Conductors	30/0.25mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation	PVC (Type T11 to BS 7655)
Insulation Radial Thickness	0.70mm
Diameter over Insulation	3.00mm (Nominal)
Number of Cores	4
Core Colours	Brown, Black, Grey & Green/Yellow
Sheath	PVC (Type TM2 to BS 7655)
Sheath radial thickness	1.00mm
Overall Dimensions	9.26mm (Nominal)
Voltage Rating	300/500V
Conductor Resistance	13.3Ω/km at 20°C (Nominal)
Cable Weight	146.2 kg/km (Nominal)
Standards	BS EN 50525-2-11 Table 4.2
Harmonization Code	H05VV-F
Sheath Colour	White
Reel Length	100m