



Product information

Erem®

503E

Code No. : **T503E**

Tip cutter - angled wide head

- The angled head provides for precise cuts at different working angles.

- Wide, robust head

Technical Data

Cut:	Flush
Length:	110 mm / 4.331 Inch
Weight:	67 g / 2.36 oz.
Angle:	30°
Length of cutting edges:	9 mm / .354 Inch
Head width:	11 mm / .433 Inch
Head thickness:	6,5 mm / .256 Inch
Head length:	19 mm / .748 Inch
Max. cutting capability	
Hard wire:	-
Medium hardness:	Ø 1,0 mm / .039 Inch
Copper wire:	Ø 1,6 mm / .062 Inch

Series 500 Medium

- Medium-size, robust, precision
- Wide range of head shapes
- Manufactured from high grade tool steel
- Cutting edges hardened to Rockwell 63-65 HRC
- Non reflecting surface, ESDsafe and resharpenable

Erem Cutters and Tip Cutters

- Internal patented Erem Magic Spring
 - Reduce costs by long life
 - Constant spring force
 - Guarantees more than 1 million operations
- High precision screw joint
 - Smooth jaw action with no play
 - Smooth cutting operation with no jaw overlapping
- Induction-hardened cutting edges in Rockwell hardness 63 - 65 HRc for exceptionally long life
- EMOS maximum opening stop limits the cutting-edge tips from opening more than 5 mm / .197 Inch. The limited extent to which the handles can open prevent user hand fatigue.
- Ergonomically shaped handles for high comfort, better grip and added safety
- Erem cut:
Options for semi flush, full flush or super flush cuts