

## DW341K Top Handle Jigsaw

- Compact, ergonomic, design gives user comfort and versatility in use
- 550 Watt motor with large power reserves gives performance and durability
- Keyless blade change with patented anti-deflection clamp design for ease of use and accuracy



## FEATURES

Compact, ergonomic, design gives user comfort and versatility in use  
550 Watt motor with large power reserves gives performance and durability  
Keyless blade change with patented anti-deflection clamp design for ease of use and accuracy  
Variable speed dial and trigger allows controlled cutting in all materials  
Adjustable pendulum action gives increased cutting performance and longer saw blade life  
Integrated sawdust blower gives a clear view of the cutting area  
Shoe bevels 45° to both left and right with presets at 0° and 45° for precise bevelled cuts  
Low profile dust extraction shield with bi-directional vacuum spout for clean, efficient cutting performance  
Heavy gauge steel shoe with anti-scratch coating and detachable anti-scratch shoe  
Can be used with a parallel guide or circular guide for accurate shape cutting  
Compatible with DEWALT flush cutting blade, DT2074 for cutting flush to an edge

## STANDARD

Blade  
Allen key  
Anti-scratch shoe cover  
Dust extraction shield  
Vacuum adaptor  
Heavy duty carrying case

## SPECIFICATIONS

Power Input	550 Watts
Power Output	350 Watts
No Load Stroke Rate	0-3100 spm
Stroke Length	20 mm
Bevel Capacity	45 °
Max. Cutting Capacity [Wood]	85 mm
Max. Cutting Capacity [Steel]	10 mm
Max. Cutting Capacity [Non Ferrous Metal]	20 mm
Weight	2.0 kg
Length	230 mm
Height	200 mm
Hand/Arm Vibration - Wood	5.5 m/s <sup>2</sup>
Uncertainty K 1 (Vibration)	1.6 m/s <sup>2</sup>
Hand/Arm Vibration - Steel	5.3 m/s <sup>2</sup>
Uncertainty K 2 (Vibration)	1.5 m/s <sup>2</sup>
Sound Pressure	98 dB(A)
Uncertainty K 1 (Sound)	3.0 dB(A)
Accoustic Pressure	87 dB(A)
Uncertainty K 2 (Sound)	3.0 dB(A)