



— PRODUCT DATA SHEET

P7R 25th Anniversary Edition



P7R 25th Anniversary Edition

PRODUCT DESCRIPTION

Shortly after the turn of the millennium, the first Ledlenser torch, the Photon Pump V8, was born - 25 years later, we re-imagined one of our most iconic models: the P7R. True to its Ledlenser heritage, it delivers brilliant light quality and output, along with a focus function that allows you to effortlessly adapt the light from spot to flood beam. It features limited edition Dark Blue housing and comes with an additional battery to ensure you never run out of light. To celebrate our heritage, we offer an exclusive 25-year warranty* - a testament to the high quality, longevity and reliability of Ledlenser products.



- Sustainable: Exclusive 25-year warranty* and use of 75 % recycled aluminium⁹
- Brilliant light quality with Spot/Flood focus function (Advanced Focus System)
- Intuitive control: Mode Select Ring for quick access to different light modes, transport lock and USB-C charging port
- Limited Edition 25-year design: Dark Blue housing
- Value pack: Includes two rechargeable batteries for double the runtime

TECHNICAL DATA	
Weight incl. batteries [g]	197
Material	Aluminum alloy
Luminous range [mm]	159
Luminous range (focused) [mm]	165
Tube diameter [mm]	27
Head diameter [mm]	35

POWER SUPPLY	
Battery quantity	1
Rechargeable	Yes
Battery type	Lithium-ion
Total battery voltage [V]	3.6
Total battery capacity [mAh]	4600
Total battery energy [Wh]	16.56 Wh
Battery replaceable	Yes
Charging time [min]	180
Energy status indicator	Battery Indicator, Charge Indicator, Low Battery Warning

SWITCH	
Front Mode Select Ring	

FURTHER SPECIFICATIONS	
IP class	IP68
Drop test (drop height) [m]	2
Working temperature range [°C]	-20 to +40

LIGHT FUNCTIONS	
Cool White Main: Boost, Power, Mid power, Low power	

LIGHT SOURCE	MAIN
Amount LEDs	1
Color	Cool White
Color temperature [K]	6000 to 7500
Color rendering index (CRI)	70

LIGHT VALUES - Cool White Main				
	Boost	Power	Mid power	Low power
Light output [lm]	2000	1200	450	25
Beam distance [m]	320	240	150	35
Run time [h]	-	2.5	5.5	80

FEATURES	
Brilliant Clarity , Intuitive Control, Sustainable, Element-proof, USB-C Charging, Flicker Free, Transportation Lock	

P7R 25th Anniversary Edition

PACKAGING AND LOGISTICS



PACKAGING INFORMATION

Type of packaging	Box
Supplied with	2 x 21700, Lanyard USB-C Charging cable
Item No.	503265
Colour	Dark Blue
STERLING RRP inc / ex vat	£129.95 / £108.29
EURO RRP inc / ex vat	€139.95 / €113.78
Customs tariff number	CTN_85131000

SINGLE PACKAGE

Dimensions W x H x D [cm]	7.2 x 21 x 4.2
Gross weight [g]	352
GTIN-13	4058205041416

EXPORT CARTON

Unit	24
Dimensions W x H x D [cm]	44.5 x 17.5 x 31
Gross weight [g]	9070
GTIN-13	4058205041393

P7R 25th Anniversary Edition

ACCESSORIES

PRODUCT CATEGORY	ITEM NO.	PRODUCT NAME
Bags & Holsters	0323	Tactical Professional Holster Type B
Chargers & Cables	502929	USB-C Adapter 20W
Mounts & Brackets	502251	Lamp Adapter Type D
Mounts & Brackets	501033	Magnetic Mount
Bags & Holsters	502269	Leather Pouch Type D
Bags & Holsters	0342	Pouch Type G
Color filters & Signal caps	502237	Signal Cone 35.1mm
Color filters & Signal caps	502238	Color Filter Set 35.1mm
Mounts & Brackets	0362	Universal Mounting System
Batteries & Accumulators	503240	21700 Li-Ion rechargeable battery 4600 mAh

SPARE PARTS

PRODUCT CATEGORY	ITEM NO.	PRODUCT NAME
Spare Parts / Products	SP502190_CLIP	Clip for P7R
Fastenings / Spare Parts / Products	SP502190_AL	Adjustable Lanyard
Charger / Spare Parts / Products	SP502910_USB	Charging Cable USB-C to USB-C
Batteries / Spare Parts / Products	900009	21700 Li-ion rechargeable battery
Protections / Spare Parts / Products	900013	Protective Elements Set Type D

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measured values according to ANSI/PLATO FL 1 in the respective setting named. If no setting is specifically named, the luminous flux (lumens/lm) and range (meters/m) values refer to the brightest setting and the burn time (hours/h) values refer to the lowest setting. A boost function (if available) can be used several times, but is only available for a short time at a time. In case the lamp is equipped with colored LED(s), the measured values are

given with white light or the white LED. If the lamp has different energy modes, the "energy saving mode" is the basis for the measurement.

2) Calculated value of the capacity in watt-hours (Wh). This applies to the battery(ies) contained in the delivery condition of the respective item or, in the case of lamps with rechargeable battery, to the battery(ies) contained herein in a fully charged condition.

9) All aluminium components are made of at least 75 % recycled aluminium and may thus vary in surface structure and color.

*) 25 year warranty with registration only, otherwise 2 years. For terms visit [ledlenser.com/en/info/service/extended-warranty25](https://www.ledlenser.com/en/info/service/extended-warranty25).