

Yoke type track rollers NATR8-PP (Series NATR..-PP)

with axial guidance, axial plain washers on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system

(http://www.ina.de/content.ina.de/en/mediathek/library/library.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	8 mm	
D	24 mm	
В	15 mm	
С	14 mm	
d ₂	19 mm	
rmin	0,3 mm	
m	38 g	Mass
Cr	5500 N	Effective dynamic load rating as track roller (radial)
w		
C0r	6600 N	Effective static load rating as track roller (radial)
w		
Cur	930 N	Fatigue limit load
n _D	7500 1/min	Speed (with continuous operation and grease lubrication)
G	7.000 17111111	Charles and Sharana and States (minimum)
		Bearing with plastic axial plain washers and optimised INA profile.
		Permissible operating temperature: -30°C to + 100°C (continuous operation).



