

Features

- 3.5 mm pitch
- Voltage Rating: 300V
- Current Rating: 7A
- Low Mating Force
- 4 WAY SCREWLESS 7A TERMINAL

RS PRO 3.5MM PITCH 4 WAY SCREWLESS 7A TERMINAL

RS Stock No.: 0631136



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Screwless PCB terminal blocks with a 3.5mm pitch and a 300V 7A electrical rating. These 3.5mm PCB terminal blocks have screwless cage clamp terminals that accept a wire size of 22 to 16 AWG.
- Standard accepts wire 22-16AWG 1.5 mm²

General Specifications

Number of Contacts	4
Number of Rows	1
Pitch	3.5mm
Mounting Type	Through Hole
Type	PCB Terminal Block
Body Orientation	Straight
Number of P	4
Gender	Male
Contact Material	Phosphor Bronze
Contact Plating	Tin plated
Housing	PA66(UL94V-0)
Colour	Grey

Electrical Specifications

Voltage Rating	300V
Current Rating	7A
Insulation Resistance	500M ohm min
Withstanding Voltage	2000V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	3.5 mm
Pin size	Please see below drawings
Pin height	3.5mm

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, CE
Declarations	Reach

Spec Drawings



