



## INSULATED SPANNER 12MM

- Open off set at 15° for easier use
- Approved for live working up to 1,000 volts
- Nonslip handle for maximum comfort
- Chrome vanadium steel construction
- Designed and manufactured to DIN3114 IEC60900 standards

Insulated Open Ended Spanner 12mm

### General information

**Country of origin:** Taiwan  
**Barcode:** 5020385044838  
**Tariff code Europe:** 8204110000  
**ECCN US:** EAR99  
**ETIM:** EC002176  
**UNSPSC:** 27111706

### Dimensions

**Net weight (g):** 57  
**Length:** 124.3 mm

### Attributes

**Product type:** Insulated Spanners  
**Material:** CrV  
**Certificates:** VDE  
**Size:** 12 mm  
**Tethering facility:** No  
**Insulated:** Yes  
**Spanner type:** Regular  
**Unit of measurement:** Metric  
**Jaw diameter:** 29.5  
**Jaw height (mm):** 8.8  
**Offset angle jaw (°):** 15

### Features



**DESIGNED IN SWEDEN**

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3  
441 39 Alingsås, Sweden