



1000 W ANGLE GRINDER

★★★★★ 4.7 (37 Reviews) [Write a Review](#)

FEATURES

- Powerful, 1000 W motor for strong performance in all applications
- Extreme compact design with an overall short length of 276 mm and 2.1 kg for most comfortable handling
- Line lock out function to prevent automatic start up after power breakdown
- Soft start for smooth start up
- Burst resistant and tool-free quick release safety guard for fast adjustment
- Ramped slide switch for easy start up, even when wearing gloves
- 4 m cable

SPECIFICATION

Specification	Current Selected Variant AG 10-125 EK
BASIC INFORMATION	
ANTI-KICKBACK PROTECTION	No
AVS ANTI-VIBRATION SYSTEM	No
BRAKE	No
DISC DIAMETER (MM)	125
LINE LOCK OUT FUNCTION	Yes
MAX. CUTTING DEPTH (MM)	33
NO LOAD SPEED (RPM)	11,000
POWER INPUT (W)	1,000
SPINDLE SIZE	M 14
STANDARD EQUIPMENT	Quick release safety guard, side handle, flange, flange nut, 4 m cable, wrench
SUPPLIED IN	No kitbox or bag supplied