

Datasheet

RS Pro Flange Mount 50Ω 7/16 Connector jack

RS Stock No: **758-1626**



Product Details

RS Pro flange-mount connector jack is designed for 50 Ω impedance applications, featuring excellent power-handling capability and low VSWR up to 7.5 GHz. This 7/16 connector provides superior performance for return loss and intermodulation distortion. It is ideal for those applications where vibration resistance and environmental protection is important, such as radio base stations and broadcast communication.

Features and Benefits

- Nominal impedance 50Ω
- Low broadband VSWR
- Vibration proof coupling

Specifications:

Body Orientation	Straight
Contact Material	Beryllium Copper
Contact Plating	Silver
Gender	Female
Impedance	50 Ω
Mounting Type	Flange Mount
Operating Frequency	0 to 7.5 GHz
Size	Standard
Dimensions	32 x 32 x 21.6 mm
Maximum Voltage Rating	2700 V
Operating Temperature Range	-55 to +155°C