

# Traditional Standard Range®

## Window Models



### Features & Benefits

- Extract / intake model in 4 sizes: 6", 7", 9" and 12"
- IPX4 Rated
- Colour: White
- Manufactured in weather-resistant polymeric materials
- For the best performance from your fan, use an Ecotronic controller
- Suitable for glass or panels up to 10mm thick

### Classic Retro-Style Ventilation

This ever popular range of extract/intake ventilating units continues to satisfy the most demanding requirements for efficient ventilation. The Vent-Axia Standard Range unit is supplied without a shutter. The shutter is available as an accessory, which can be easily fitted within the unit.

Standard Range Window fans are suitable for most forms of single glazing or can be wall mounted in a Vent-Axia fixing plate. Vent-Axia's patented spigot and ring method of fixing ensures easy installation and a weather proof joint. The simple integrated component design makes installation and servicing easy.

### Performance

Model	Extract Performance m <sup>3</sup> /h (l/s) F.I.D.	Watts MAX.	Sound dB(A) @ 3m	Amps @ 240V
S6WW	285 (79)	32	35	0.16
S7WW	425 (118)	34	31	0.16
S9WW	710 (197)	53	39	0.24
S12WW	1560 (433)	84	42	0.36

### Motor

Purpose designed enclosed motor. Suitable for running at any angle. Quiet running.

Supply voltage 220-240V/1/50 Hz. Suitable for operation in ambient temperatures from -40° to +50°C. Fitted with Standard Thermal Overload Protection (S.T.O.P.).

### Shutter Type SD/R

The extract/intake shutter fits inside the Vent-Axia unit and closes against unwanted back draughts. It can be fitted at the same time as the unit or at a later date if required.

Airflow operated for extract use, cord operated lock for intake use. For all models mounted in vertical surfaces only.

### Controller

The Ecotronic controller is recommended for use with this model to provide full function control of the fan plus the option of sensor mode using a selection of electro-mechanical switches to provide automatic switching of the fan.

Alternatively, single speed extract is achieved using a normal On/Off switch.

### Easy Cleaning

Integrated component design allows all parts to be dismantled for cleaning without the use of specialist tools.

### Protective Grilles

Where Standard Range units are installed in low positions, finger guards provide extra protection to VDE, DIN 31001.

### Models

Size	Stock Ref
S6WW	131310
S7WW	132310
S9WW	133310
S12WW	134310

### Shutters

Size	Stock Ref
S6SD/R	231710
S7SD/R	232710
S9SD/R	233710
S12SD/R	234710

### Dimensions (mm)

Size	6 in	7 in	9 in	12 in
A	140	147	166	201
B Ø	216	254	295	381
C	21	21	21	21
D	83	83	92	105
E (max)	10	10	10	13
Fixing hole Ø	184	222	260	337
Weight kg	2.9	3.2	4.6	7.0

