

Features

- IP68
- Maximum 72 Fibres
- ABS/PP Construction

RS PRO Fibre Optic Splice Enclosure

RS Stock No.: 0143847



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This product is suitable for the connection of overhead, pipe and buried straight and branch. The box body and base are sealed with hoops and rubber. The closure casing is made of quality engineering plastics, and has good performance of anti-erosion against acid and alkali salt, anti-aging. The mechanical structure is reliable and has the performance of resisting wild environment and intensive climate changes and serious working environment. The splice trays (FOST) inside the closure have an adequate curvature radius and space for winding optical fibre to make sure the curvature radius for optical winding 40 mm. Each optical cable and fibre can be operated individually. The product can be opened again and reused after installation.

General Specifications

Type	In-Line Fibre Optic Splice Enclosure
Material	ABS / PP
Number of Fibres per Tray	24 Single Core
Number of Trays	4
Maximum Number of Fibres	72
Sealing of Ports	Rubber Seal
Sealing of Shell	Silicon Rubber
IP Rating	IP68
Height / Width / Depth	480mm x 155mm x 110mm

Approvals

Standards Met	CE UKCA REACH ROHS
---------------	--------------------

Similar Products

Stock No.	Brand	Product Name
0143847	RS PRO	72 Fibre Optic Splice Enclosure

