



PCT-0200-050-BL-100

E1517952

Cable Tie, 200x4.8mm, Blue Plastic Barb



Product Properties:

Detectable	No
Min. tensile strength	220 N
Model	Internal toothing
Material quality	Polyamide (PA)
Operating temperature	-40-85 °C
Band closure	Plastic lip/-cam
UV-stable acc. ASTM D6779	No
Transparent	No
Fluorescent	No
Solvable fastener	No
Text strip	None
Type of fastening	None
Colour	Blue
Surface protection	Untreated
Material	Plastic
Halogen free	Yes
Max. tensile force	220 N
Inflammability class of insulation material according to with UL94	V2

Dimensions:

Bundle diameter	2-54 mm
MOQ	100 .

Unit	pcs
Length belt/tape/tie	200 mm
Band width	4.8 mm
Max. tensile force	220 N

Approvals:

Approved according to UR	Yes
UL approval	Yes
Approved according to CE	Yes
Inflammability class of insulation material according to with UL94	V2

Compliance:

CA Proposition 65	In compliance
Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
PFAS	No PFAS
PFOA	No PFOA
PFOS	No PFOS
POPs	No POPs
REACH	No SVHC (247 Subs. 21 Jan 2025)
REACH Annex XIV	No REACH Annex XIV
REACH Annex XVII	No REACH Annex XVII
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000046 - Cable tie
ETIM-Release	10.0
Trademark	NEMIQ
Product Group	Cable ties, PCT & CT
Alternative SKU	PCT-0200-050-BL-100
E-no	E1517952

Logistic information:

Barcode	733117640075
Country of origin	CN
E-no	E1517952
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	100 .

Stock code	PCT-0200-050-BL-100
Taric code	39269097
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.