



## Outdoor Pendant E27 Black 3M with plug IP44

Article number: 143003

BAI Pendant Light Outdoor IP44 E27 Black with 3M Rubber Cable 2x1.0mm<sup>2</sup> and Plug CLII Max 25W

The outdoors is getting more important and the outdoor living season is getting longer. They also want to bring the atmosphere inside out. Light helps with that. The trend of a beautiful LED lamp on a cord that is going on indoors can now also be continued outdoors thanks to the Outdoor Pendant by Bailey. This IP44 rubber cable with plug and lamp base is available in 3 and 5 meters. Ideal for under coverings or on trees to enhance the atmosphere outside.

### General ETIM properties

ETIM group	Luminaires
ETIM class	Pendant luminaire
Name	Outdoor Pendant E27 Black 3M with plug IP44
Brand	Bailey
Productseries	BaiLum pendant
Producttype	Outdoor

## ETIM specifications

Housing colour	Black
Lamp holder	E27
Housing material	Plastic
Suitable for workplace according to EN 12464-1	No
Lamp type	LED exchangeable
Pendant length [mm]	3000 - 3000
With light source	No
Suitable for number of light sources	1
Suitable for light line configuration	No
Material cover	Without cover
Type of grid	None
Voltage type	AC
Nominal voltage [V]	220 - 240
Type of control gear	Not required
With control gear	No
Exchangeable control gear	No
Dimming 0-10 V	No
Dimming 1-10 V	No
Dimming DALI	No
Dimming DALI-2	No
Dimming DMX	No
Dimming programmable	No
Dimming DSI	No
Dimming RF	No
Dimming potentiometer (integrated)	No
Dimming manufacturer's proprietary system	No
Dimming mains voltage modulation	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming with push-button	No
Light distributor	None
Reflector	None
Light distribution	Symmetric
Light outlet	Direct
Direct-/indirect proportion separately controllable	No
Degree of protection (IP)	IP44
Impact strength	IK02
Protection class according to IEC 61140	II

Luminaire with limited surface temperature, sign "D" according to EN 60598-2-24	No
Suitable for emergency lighting	No
Filament test according to IEC 60695-2-11	None
Suitable for lamp power [W]	1 - 25
Length [mm]	55
Diameter [mm]	39
With suspension	Yes
Type of wiring	Ending
Number of poles	2
Conductor cross section [mm <sup>2</sup> ]	0.75
Connection type	Other
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Operation by Bluetooth	No
Dimmable	No
Containing product according to 2019/2020/EU	No
Emergency power supply system	None
With movement sensor	No
With presence detector	No
With light sensor	No
Connectable conductor cross section [mm <sup>2</sup> ]	0.5 - 0.75
Compatible with Casambi	No


### Alternative articles



143002

Outdoor Pendant E27 Black 5M  
with plug IP44

### Complementary articles



145417

Mini-shade for pendant 190 Black



141887

LED FIL Safe A60 E27 4W (39W)  
450lm 827 PC Clear

