



Product data sheet

Power tools for trade & industry

Chainsaw

PRO GKE 18V-40



Powerful 18V Brushless chainsaw for a wide range of applications

The most important data

Chain speed	12.4 m/s
Chain pitch	3/8" (9.52 mm)

Order number 0 600 8D3 000

Technical data

Additional data

Battery recommendation	$\geq 5.5\text{Ah}$
Chain pitch	3/8" (9.52 mm)
Chain speed	12.4 m/s
Chain gauge	1.1 mm

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Brushless motor delivers strong performance for a wide range of applications – with low noise level and without exhaust fumes
- Equipped with a 40 cm bar for continuous cutting through beams, timber, and thick branches
- OptiCut makes sure that the tool does not stop abruptly with higher workloads, but automatically adjusts speed and torque

