



8910DP32V09

CONTACTOR 600VAC 30AMP DP +OPTIONS



Download your 8910DP32V09 datasheet



Characteristics | Documents & Downloads

Main

Hide

Product or component type	Definite Purpose Contactor
[In] rated current	30 A
Motor power hp	2 hp 115 V AC 1 phase 5 hp 230 V AC 1 phase
Poles description	2P
Pole contact composition	2 NO
Control circuit voltage	220 V AC 50 Hz 208...240 V AC 60 Hz

Complementary

Hide

Product certifications	CE CSA UL listed
Locked rotor rated current	125 A 460 V AC 120 A 575 V AC 150 A 277 V AC
[Ue] rated operational voltage	600 V AC
Network number of phases	1 phase
Electrical connection	Quick connect terminals
Range of product	DP

Offer Sustainability

Hide

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Hide

Period	18 months
--------	-----------