

Rexel Momentum Extra XP426+ Jam Free Cross Cut Paper Shredder

Rexel Momentum Extra jam free paper shredders are ideal for destroying confidential documents in the office. The XP426+ shredder machine shreds up to 26 sheets of A4 paper (80gsm) in one go through the manual feed slot into P-4 (4x35mm) cross cut pieces. Active sensing technology measures the number of sheets being fed in real-time to stop paper jams and misfeeds; indicated by a red LED on the control panel. This paper shredder will not operate until the number of sheets is reduced below or at the maximum sheet capacity. This cross cut shredder is designed for moderate to heavy use with its high sheet capacity, large 120L bin size and continuous run time. There's no need to remove staples and paper clips first; this Rexel shredder also safely shreds CD's, DVD's and credit cards through a separate feed slot.



Attributes

- Shreds up to 26x A4 sheets (80 gsm) at once.
- P-4 cross cut (4x30mm)
- Jam-free active sensing technology measures the number of sheets being fed in real-time to stop paper jams and misfeeds; indicated by a red LED on the control panel.
- This paper shredder will not operate until the number of sheets is reduced below or at the maximum sheet capacity.
- This heavy duty paper shredder also shreds credit cards, staples, paperclips and CD's/DVD's.
- 120L capacity bin with cabinet door for easy emptying (1100 x A4 sheets).
- Continuous run time with fan cooling and ECO mode to save power when not in use.
- Touch control panel
- 55 dBA ultra-quiet noise level
- Infra red bin full sensor
- Manual reverse / forward feature
- 2 year warranty, 2 year cutter warranty



Specifications

Number	2021426XEU
Colour	black
Dimensions (W x H x D)	553 x 1028 x 510 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	310
Run Time From Cold (min)	Continuous more than hr
Shredded Particle Width mm	4x30
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	29
Cutting Capacity sheets (80gsm paper)	26
Container/collection volume in l	120
Shreds	Paper, DVDs/CDs, Credit cards, Paper clips & Staples
Power consumption (W)	600
Noise Level (dBA)	55
Period of Warranty (Years)	2
Location	Large Office
Number Of Users	10+
Shredder Features	Wheels, Touch Control, Jam Free Technology
Weight	59000 g
Pallet quantity	1
EAN code	5028252625654