

# MQDC-801-5M-PRO

► PRODUCTS FOR INDUSTRIAL AUTOMATION



Cordset: Double-Ended M12  
 8-pin Straight Female; 5-pin Straight Male  
 0.3 m 4x22 Black PVC Jacket  
 Nickel-Plated Brass Coupling Nuts  
 Part Number: 807201

CERTIFICATIONS



SPECIFICATIONS

IP Rating	IP67
Connector 1 Type	M12
Connector 2 Type	M12
Number of Ends	Double Ended
Connector 1 Number of Contacts	8
Coupling Nut Material	Nickel Plated Brass
Connector 2 Number of Contacts	5
Cable Jacket Material	PVC
Connector 1 Thread/Snap	Threaded
Cable Jacket Color	Black
Connector 2 Thread/Snap	Threaded
Number of Conductors	4
Connector 1 Key Code	A
Wire AWG	22
Connector 2 Key Code	A
Connector 1 Gender	Female
Outside Cable Diameter (mm)	5.21
Connector 2 Gender	Male
Cordset Length (m)	0.3
Connector 1 Orientation	Straight
Connector 2 Orientation	Straight
Overmold Material and Color	PUR Black
Minimum Temp. (Celsius)	-40
Maximum Temp. (Celsius)	70



<b>Current Rating (A)</b>	2
<b>Supply Voltage</b>	30 V dc
<b>Item Status</b>	RELEASED
<b>Application</b>	Signal
<b>Connector 1 Body Size</b>	Standard
<b>Connector 1 Overmold Material and Color</b>	PUR Black
<b>Connector 1 Coupling Nut Material</b>	Nickel Plated Brass
<b>Connector 2 Body Size</b>	Standard
<b>Connector 2 Overmold Material and Color</b>	PUR Black
<b>Connector 2 Coupling Nut Material</b>	Nickel Plated Brass
<b>Feature: Washdown Rated</b>	No
<b>Oil/Grease Resistant</b>	No