



Measurement technology - AC/DC current transformers

Status: **Available** Data sheet created: **01.07.2025**

Item Number: 2800010 - Serie: SensAct - EAN: 9008662014114



- ✓ AC/DC current transformer TRMS, 0 to 50A
- ✓ measuring frequency DC or 20-2000 Hz
- ✓ bipolar
- ✓ analog 0-10V and Modbus RTU / RS485 interface
- ✓ measuring range adjustable by DIP switch or RS485
- ✓ DIN rail mounting

Description

Precise and reliable reading of mechanical, electrical and electronic measured values with analogue and digital evaluation options.

General information

Short description	AC/DC current transformer 50A with ModBus RTU/RS485 and 0-10V
Item Number	2800010
EAN	9008662014114
Main category	Measurement Technology
Series	SensAct
Type	S6IA50AM
Supply	12-30V DC



Ambient conditions and general specifications

Pollution degree 2, pollution level can be increased by installation in suitable enclosures (according to IEC 60664-1)

Logistics

Minimum Quantity	1
Tariff Number	85437090
EAN	9008662014114
Country of Origin	IT
Product Weight (g)	88

Available declarations / conformities

CE	✓
REACH	Open document
WEEE	Open document
TSCA	Open document
RoHS	Open document
CMRT	Open document

Further documents

Modbus register S6IA50AM [Download document](#)

CAD Files

STEP_S1MM_en.stp	Download file
STEP_S6IA_en.stp	Download file
STEP_S6IA_en.stp	Download file
STEP_S6XM_en.stp	Download file
STEP_S9IA_en.stp	Download file
STEP_S9XM_en.stp	Download file

