

6 46X50

Double open ended spanner

metric

Code	ETIM
6068710	EC002130
EAN	UNSPSC
4010886606872	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-04
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3110, ISO 3318, ISO 1085, ISO 10102
- With flat heads
- Satin non-glare finish
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Secure grip thanks to slim profile shaft
- Overloading indicated by deformation
- Top-grade industrial quality for the hardest of continuous use
- Chrome-vanadium steel 31CrV3

Article information

Contents (Qty of pieces)	1	Width across flats 1 [mm]	46
Net weight [kg]	1,445 kg	Width of head 2 [mm]	102 mm
Total length [mm]	449 mm	Head height 1 [mm]	11,6 mm
Total width [mm]	100 mm	Width of head 1 [mm]	95,5 mm
Total height [mm]	12 mm	Width across flats [mm]	46x50
Material	31CrV3	Width across flats 2 [mm]	50
Standard	DIN 3110	Mouth position 1	15°
	ISO 3318		
	ISO 1085		
	ISO 10102		