

M18 FHIW2F12-502X

M18 FUEL™ 1/2" HIGH TORQUE IMPACT WRENCH WITH FRICTION RING

- Great power density: the M18 FUEL™ high torque impact wrench delivers 1491 Nm fastening torque and 2034 Nm of nut-busting torque in a compact size of 193 mm, which gives more access in tight spaces
- 2000 RPMs of no load speed to perform your task 35% faster than with the previous gen
- Our battery isolation system provides a secure battery connection and controls vibration transmitted to the pack
- Robust gearcase for more durability
- Tri-LEDs deliver high-definition lighting to increase workspace visibility
- 4-Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility
- Mode 4 bolt removal, provides maximum nut-busting torque then shifts to 750 rpm for outstanding control when removing fasteners
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



No load speed (rpm)	0-700/ 0-1300/ 0-2000/ 0-2000
Impact rate (ipm)	0-1300/ 0-2200/ 0-2400/ 0-2400
Max. torque (Nm)	
Nut-busting torque (Nm)	2034
Weight with battery pack (EPTA) (kg)	3.4 (M18 B5)
Kit included	2 x M18 B5 Battery packs, M12-18 FC Charger, HD Box
Article Number	4933492783