




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2324579-6
HOUSING, PLUG, 26P, DUAL ROW,
EP2.5



TE Part # 2-1969543-6
ASSY, HDR, VERT, BOSSED, DUAL
ROW, EP2.5



TE Part # 2-1969592-6
HSG,REC,FREE-HANGING,DUALROW,
EP2.5



TE Part # 2-1969572-6
ASSY, HDR, RIGHT ANGLE, DUAL
ROW, EP2.5



TE Part # 2-1969582-6
ASSY, HDR, VERT, NO-BOSS, DUAL
ROW,EP2.5



TE Part # 2-1969540-0
HOUSING, PLUG, 20P,DUAL ROW,
EP2.5



TE Part # 2-1969594-6
HSG,REC,PANEL MOUNT,DUALROW,
EP2.5

Customers Also Bought




TE Part #2-2013311-1
EMBOSS TAPE DDR3 204P 9.2H RVS



TE Part #6-2176379-7
RQ 0805 523R 0.1% 10PPM 5K RL



TE Part #9-2176092-0
RP 2A 0.25W 6K98 0.1% 25PPM 1K RL



TE Part #5499160-1
A/L UNIV HDR 10P VERT SHT LAT



TE Part #1-2301994-1
RJ45 JACK INT.MAG. 1GB LED 1X1
INV (LOW)



TE Part #1376009-1
DYNAMIC D2100 HDR H ASSY 8P X



TE Part #ANT-916-CW-HW-SMA
Antenna 1/2 Wave Whip Whip
916MHz SMA



TE Part #1-1623925-6
CFR100 5% 1K2



TE Part #1-770170-0
03P MINI-UMNL ASSY VO SNNI*



TE Part #5745410-7
09 PLUG SP/MS STD

Documents



Product Drawings

HOUSING, PLUG, 26P,DUAL ROW, EP2.5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1969540-6_A_c-2-1969540-6-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1969540-6_A_c-2-1969540-6-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1969540-6_A_c-2-1969540-6-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773461-6_EP2.5_Connector_Series

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

VDE Certificate

English