



ENGLISH

Datasheet

RS Pro Pro Slim line Frameless Floodlight 10W

RS Stock No: 145-5878



This RS Pro LED 10W Floodlight has an ultra slim line body for an aesthetically pleasing look. This floodlight is ideal for industrial and commercial applications. It is suitable for outdoor use. Available as standard or with PIR.



ENGLISH

Typical Properties

Material	Aluminium & Toughened Glass
Wattage	10 W
Beam Angle	110°
Lumen Output	900 Lm
Lamp Type	LED
Voltage	240 V
Colour Temperature	4000K
Operating Temperature	-20° - 40°C