

Datasheet


RS 15m Black HDMI DVI Video Cable Assembly Male to Male HDMI to DVI

Stock Number: 489-438



Connector A	Male HDMI
Connector A Gender	Male
Connector A Type	HDMI
Connector B	Male DVI
Connector B Gender	Male
Connector B Type	DVI
Current Rating	0.5 A
Length	15m
Sheath Colour	Black

REVISIONS			
DATE	LTR	DESCRIPTION	APVD
2008/01/03	A	New Drawing.	TOM
2008/01/17	B	Add specifications	



- Note: 1.HDMI-19P Mould No.:DM₁-H1011.
 2.DVI-(18+1)P Mould No.:DM₁-H591
 3.DVI-(18+1)P One Side Molding LOGO* ④*,
 Other Side Molding Blank LOGO.
 4.RO=RoHS.

Table:

PART NO	ITEM NO	LENGTH
489-406	P-A6C068-6-AL10M	10000±100
489-438	P-A6C068-6-AL15M	15000±150

- specifications:
 1.bandwidth up to 5 Gbps
 2.10,000 Cycles
 3.Gold-plated contacts
 4.Lead-Free plating
 5.Tray and embossed packaging
 6.Current: 0.5A
 7.Voltage:40V



No	Part No	Title	Description
15	NA360030	Paper Tape	Paper Tape,Single Side With Adhesive.W12*L130mm-RO
14	NA360030	Paper Tape	Paper Tape,Single Side With Adhesive.W12*L100mm-RO
13	GC300160	Copper Foil	Copper Foil.W30*L70mm-RO
12	GC300160	Copper Foil	Copper Foil.W30*L60mm-RO
11	JAB60020	H.S.T	Black Heat Shrink Tube OD:1.5mm-RO L:10mm
10	JAB60870	H.S.T	Black Heat Shrink Tube OD:0.8mm-RO L:15mm
9	JAB60380	H.S.T	Black Heat Shrink Tube-RO.Ø2.5*L8mm
8	GC330030	Stick	Tin Stick-RO
7	NA002640	Screw	DVI Thumb Screw 2.8*32mm-RO #4-40UNC Black
6	JB513960	PVC	PVC 45P-RO Black(T-000)
5	J1190010	PE	Transparent PE-RO
4	GC340080	Tin	OD:0.6mm-RO
3	1B370070	Conn.	DM-(18+1)P-N-GS-K-S-RO Black Insulator,Solder Type,Shell Plated Nickel
2	1J280210	Conn.	HDMI-19PSS24-K-A-RO W/PCB Shell Plated Nickel>Contact Gold Plated 15u"
1		Cable	UL20276 (1P#24+AL+DH+MLAR)4C+1P#24+5C#24-RD+AL+B 009.5 Black(T-000) Len

UNLESS OTHERWISE SPECIFIED
 TOLERANCE :
 X .X ±0.2 ANGLES : 8°
 X.X ±0.1
 X.XX ±0.05 DO NOT SCALE DRAWING

Jack

THIRD ANGLE PROJECTION

SCALE

DATE

RoHS

OEM CABLE ASSEMBLY C3110

489-4XX E

P-A6C068-6-ALXXM 05/21/2008