

Grass shear LXT®

DUM111RTX

18V • 2 500 min⁻¹ • 110 mm

A handy and light tool for grass trimming and cutting.

Lightweight and compact LXT® Grass shear for various jobs. Dual blade action cuts quickly with a shearing effect. Toolless blade changing system enables simple and easy blade changes. One 5.0 Ah battery and a charger.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2500 min ⁻¹
Cutting width	110 / 200 mm
Cutting height positions	3
Mowing Height	15 - 25 mm
Sound Power Level (L _{WA})	79 dB(A)
Sound Pressure Level (L _{pA})	70 dB(A)
Product net weight	1,0 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,8 kg
Product Dimensions (L x W x H):	347 x 120 x 130 mm
Vibration Level (3 axes)	≤ 2,5 m/s ²

User benefits

- Compact and lightweight design
- Tool-less blade changing system enables simple and easy blade changes
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381738989

Link to product - www.makitauk.com



Related products

■ Standard AC

458342-0
Blade Cover



■ Standard MA

BL1850B
Battery LXT® 5,0 Ah



DC18RC
Battery Charger LXT®



■ Optional AC

191N24-2
Shear Blade



458342-0
Blade Cover



■ Other

User manual

Parts drawing