

eTAU108

Slim External DVD writer



Available in Black and White

Super AllWrite



The Ideal Travel Accessory

Archive Your Movies, Photos, and Music Anytime

Lite-On External Top-Load DVD/CD Writers are extremely portable and compatible with CD, DVD and Double Layer DVD formats (up to 8,5 GB).

With these Lite-On External Top-Load DVD/CD Writers users can burn files to discs, install software, listen to their music CDs, and watch DVD movies on the go. No power adapter needed!

The eTAU108 features a unique top loading mechanism, which is not only ergonomic, but also offers stability and reliability during long time operation.

The fully featured Lite-On eTAU08 drive comes with the latest optical storage technologies.

External Top Loader Design

- Highly portable and ergonomic design
- Insert media via top loading mechanism
- Robust casing of quality materials. Ideal as a travel accessory

USB bus-powered

- No power adapter needed!
- Your notebook or netbook is your power source

Super AllWrite

- Super AllWrite is the compatibility standard from Lite-On to offer the ability to read, write and re-write to any disc format on the market,
- Use your DVD writer for any purpose with the media you desire (including CD-R, CD±RW, DVD±R, DVD±RW, DVD±R DL & DVD-RAM)
- Purchase your media without hassle; you no longer have to worry about compatibility

USB 2.0 connectivity

- Higher transfer rates with USB 2.0 connection (compared to USB 1.1)
- The external USB 2.0 interface allows you to easily connect to any PC, anywhere



USB Powered; No Power Adapter Needed!



Conveniently Store Your Cable at the Bottom of the Drive

eTAU108

Slim External DVD Writer

Technical Specifications

DVD Family	Write	
	DVD+R	8X maximum by Zone CLV
	DVD-R	8X maximum by Zone CLV
	DVD+R9	6X maximum by Zone CLV
	DVD-R9	6X maximum by Zone CLV
	DVD-RAM	5X maximum by Zone CLV
	ReWrite	
	DVD+RW	8X maximum by Zone CLV
	DVD-RW	6X maximum by Zone CLV
	Read	8X maximum by CAV
CD Family	Access time	
	1/3 Stroke : 180ms Full Stroke : 310ms Random Access : 180ms	
	Write	
	CD-R	24X maximum by CAV
	ReWrite	
	CD-RW	24X maximum by Zone CLV
	Read	24X maximum by CAV
	Access time	
	1/3 Stroke : 180ms Full Stroke : 310ms Random Access : 180ms	
	PC Required	
General	Pentium 4 1.3GHz or higher CPU and 128MB or higher RAM are required.	
	HDD must have access time < 20ms; with a minimum of 100MB free space.	
	9GB free space for creating a DVD image file (9GB for double layer; 5GB for single layer).	
	Compatibility	
	Microsoft Windows 2000 SP 4 / XP / Vista & Linux	
	MTBF (Life)	
	60000 POH	
	S/N Ration	
	> 60dB	
	Environment	
	Operating	5°C to 35°C; Relative Humidity: 10% to 80%
	Non-Operating	-40°C to 65°C; Relative Humidity: 10% to 90%
	Dimension	142.1(W) x 19.4(H) x 143.8(D) mm
	Weight	< 0.35Kg



©2009 by PLDS Corporation.

Designed by Philips Lite-On Digital Solutions Corporation.

The information contained herein is subject to change without notice. PLDS cannot be held responsible for any technical errors or omissions contained herein. Trademarks are property of their respective owners.