

---

Item no.: 2002-2201  
Product description: Double deck terminal block through/through I/I without marker carrier housing color: gray suitable for Ex e applications

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Current intensity EN	28 A
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Number of levels	2
Cross section [mm <sup>2</sup> ]	0.25 - 2.5 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm <sup>2</sup> ]	0.25 - 4 mm <sup>2</sup>
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	10.119 g
Color	grey
Wiring type	Front-entry
No. of connection Points	4

No. of potentials	2
Height	52 mm
Height	2.047 in
Width	5.2 mm



Width	0.205 in
Depth	70 mm
Depth	2.76 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2002-2201	AEX	E185892	550	20	22-12
2002-2201	CCA	NL6387	500	24	0,2-2,5/4
2002-2201	CSA	154112-1536069	600	20	22-12
2002-2201	GL	6187-05HH	500	24	4,0
2002-2201	KEMA	NL2116586.02	500	24	0,2-4
2002-2201	LR	91/20112(E6)	500	24	0,4
2002-2201	PTB	IECEXPTB03.0004U	440	20	0,2-4
2002-2201	PTB	PTB03Atex1162U	440	20	0,2-4
2002-2201	RosTest	8189158	440	20	0,2-4
2002-2201	UR	E45172	300	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected