


# axial kit EAMM-A-D32-40P

Part number: 1976465

☆ Core product range

Suitable for electric drives.

FESTO



## Data sheet

Feature	Value
Assembly position	Any
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	1.6 Nm
Product weight	160 g
Interface code, actuator	D32A D32B
Interface code, motor in	40P
Materials note	Contains PWIS substances Conforms to RoHS