



Part No. 112090300

Series 209 Hi-vis guns

3D

PDF

Inquiry List

Class title
Regulator
Tube
Removable tube
Connection
Rc 1/4"
Noise level (db)
87 dB
Flow capacity (l/min)
232 l/min
Max working pressure (bar)
8 bar (116 PSI)
Standards
OSHA STD 01-13-001

Min. burst pressure (bar)

32 bar (928 PSI)

Material

POM (body), TPE (soft grip), brass (tube)

Media

Air and non-explosive water based liquids

Min temperature (C)

-20°C — +60°C (-4°F — +140°F)

209 Hi-vis guns

The hi-vis version of the 209 air and fluid guns ensures increased visibility and promotes safety in the workplace. The hi-vis gun incorporates OSHA-compliant safety nozzles, which significantly reducing the risk of air embolism-related accidents and injuries. The durable yet lightweight plastic body makes it easy to handle and maneuver. It can withstand rough handling and is designed to be long-lasting, even in demanding environments. The 209 blow gun is a versatile tool that can be used for various applications. It can be used with both air and non-explosive fluids, making it a versatile solution for many industries.



Check with an authorized CEJN distributor for availability and prices. All measurements are in mm. Other connections and sealing material on request. Some part numbers may be subject to minimum order quantities. CEJN reserves the right to make changes without further notification. Thread connections are listed according to ISO standards, unless stated otherwise.