


# CD-HF 120X80 BU - Cable duct

3240608

<https://www.phoenixcontact.com/gb/products/3240608>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, blue, halogen-free, comprising upper part and mounting base, width: 120 mm, height: 80 mm, length: 2000 mm

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240608             |
| Packing unit                         | 8 pc                |
| Minimum order quantity               | 8 pc                |
| Sales key                            | BE7442              |
| Product key                          | BE7442              |
| Catalog page                         | Page 579 (C-3-2019) |
| GTIN                                 | 4046356630245       |
| Weight per piece (including packing) | 1,956 g             |
| Weight per piece (excluding packing) | 1,766 g             |
| Customs tariff number                | 39259020            |
| Country of origin                    | DE                  |

# CD-HF 120X80 BU - Cable duct

3240608

<https://www.phoenixcontact.com/gb/products/3240608>



## Technical data

### Product properties

|              |             |
|--------------|-------------|
| Product type | Wiring duct |
|--------------|-------------|

### Dimensions

|        |         |
|--------|---------|
| Width  | 120 mm  |
| Height | 80 mm   |
| Length | 2000 mm |

### Material specifications

|                                                        |                  |
|--------------------------------------------------------|------------------|
| Color                                                  | blue (RAL 5015)  |
| Material                                               | PC/ABS           |
| Flammability rating according to UL 94                 | V0               |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1, HL 2, HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1, HL 2, HL 3 |
| Components                                             | halogen-free     |

### Cable/line

|              |     |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

### Mechanical properties

|                                        |                                    |
|----------------------------------------|------------------------------------|
| Usage cross-section                    | 8676 mm <sup>2</sup> (100 %)       |
| Number of cables at 60% filling volume | 318 (2.5 mm <sup>2</sup> Ø 3.4 mm) |

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C |
|---------------------------------|------------------|

# CD-HF 120X80 BU - Cable duct

3240608

<https://www.phoenixcontact.com/gb/products/3240608>



## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240608>



**CSA**

Approval ID: 80202282



**VDE approval of drawings**

Approval ID: 40058453

**DNV**

Approval ID: TAE00004VN



**UL Recognized**

Approval ID: E328576

# CD-HF 120X80 BU - Cable duct

3240608

<https://www.phoenixcontact.com/gb/products/3240608>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400703 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000012 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131700 |
|-------------|----------|

# CD-HF 120X80 BU - Cable duct

3240608

<https://www.phoenixcontact.com/gb/products/3240608>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)