



Datasheet  
**196-4197**  
RSPRO-F22R



## USB Rechargeable Focus Flashlight

 **3200**  
LUMENS

 **4** Light  
Settings

 **IPX7**  
Water Proof

 USB Power Bank  
Output: 5v

 USB Charging  
Cable Inc.



### Technical Data

3200 Lumen white Osram P8 LED  
Tough aircraft-grade aluminium construction  
Easy twist flood-to-spot focus  
White daylight 5500k colour temperature  
Glow-in-the-Dark reflector  
Easy press rubberised switch on torch body  
Flawless domed lens for long distance beam  
Safety wrist strap included  
Power Bank feature  
Charging indicator lights  
1m impact resistant

**Product Size:** 47 x 47 x 242 mm

**Product Weight:** 402g

**Battery:** 2 x 3.6v 2000mAh 18650 Li-ion Batteries with 2.8V protection board (included)

**Charger:** Micro-USB cable (included) Max 1A

**Charging Time:** approx 4.5 hrs

**LED Charging Indicator:** Red-Charging, Green-Fully charged

MODE			
HIGH	3200 lm	250 m	1.5 hrs
MEDIUM	320 lm	88 m	3.5 hrs
LOW	50 lm	30 m	50 hrs
STROBE	--	--	4 hrs

### Operation

High > Medium > Low > Off

If left in any MODE for 8 or more seconds, the next press will turn OFF.

Strobe Function - double press at any time to enter strobe mode

### ADVICE & IMPORTANT INFORMATION!

- Do not look directly at the LED.
- Do not operate in direct sunlight or extreme temperature conditions (below -10°C or above 40°C).
- The LED will become hot when switched on; do not touch and do not place face down on any surface - risk of fire!
- Do not use the device if there is any visible damage to the housing or cable.
- The aluminium housing can get warm. If it gets too hot turn down the brightness or turn off and allow to cool.
- Do not use the lamp in the immediate vicinity of flammable materials or gases.
- Children under 12 years of age should only use the product under adult supervision.
- Before cleaning the product, disconnect the charge cable. Clean with a dry or slightly moist, clean, lint-free cloth and a mild detergent if required. Do not use cleaners that contain abrasives or solvents.
- Do not attempt to modify the product; this will void any warranty and can be dangerous.
- Improper use or modification is not covered under warranty.
- Ensure the lens does not come into contact with hard/sharp objects; damage to the lens may affect light output.
- To maintain rechargeable batteries, distributors should recharge the battery every 6 months and users should recharge every 3 months if not using for an extended period.
- Fully charge the product before storage.
- The rechargeable battery will reach optimum performance only after several complete charging and discharging cycles.
- Protect the battery from heat, intense sunlight, fire, water and moisture - danger of explosion!
- If the battery is damaged, fluids can leak out. AVOID contact as this can lead to skin irritation and/or burns. If skin contact happens, rinse thoroughly with water. If irritation persists, seek medical advice. Also seek immediate medical assistance if battery fluid comes into contact with the eyes.
- Do not dispose of this device in normal household waste. It must be disposed of via an authorised disposal centre or at your local waste disposal unit.
- Please recycle packaging where possible. Keep these instructions for future reference or for subsequent possessors.

