

Datasheet

RS Pro Stainless Steel Countersunk Head Machine Screws, M5 x 60mm

RS Stock No: **914-1699**



Product Details

RS Pro machine screw measuring M5 x 60 mm, is made of type 304 S15 A2 grade 18//8 stainless steel. The countersunk head screw can be used at up to 800°C. The slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- A2 grade 18/8 stainless steel (Type 304 S15) construction
- Can be used up to 800°C
- Suitable for use in most food, medical, chemical, construction and electronic applications



ENGLISH

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Countersunk
Material	Stainless Steel
Length	60 mm
Stainless Steel Type	304 (A2)
Thread Pitch	0.8
Thread Size (Metric)	M5
Head Diameter	8.94 to 9.3 mm
Head Height	2.7 mm
Slot Depth	1.1 to 1.4 mm
Slot Width	1.2 mm
Specification	DIN 963