

Features

- Serrated jaws for improved grip.
- Compatible with square and hex head nuts to M12 (19mm) and 3/4".
- Jaws case hardened to HRC 40-44 for durability.
- Chemically blackened jaws and handles, with plastic grips for added comfort.

RS PRO Spanner Quick Grip No.1

RS Stock No.: 0606319



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

RS PRO Spanner Quick Grip No:1

A plier-type spanner engineered to effortlessly grip nuts and bolts of non-standard & hexagon sizes with precision and ease. A comprehensive wrench set in one compact plier. Engineered with serrated jaws for a vice-like grip. Soft plastic grips for added comfort.

Benefits

- Ideal for handling non-standard, hexagon & square sizes.
- Unique plier type design, offering a quick fitting grip for a range of fixings.
- Comfortable and easy to use, with exceptional gripping power.
- Built to last, with robust construction and a rust-resistant finish.

Applications

An innovative toolbox essential, with rugged construction, that is versatile and convenient, ideal for:

- Electronic communications and IT applications.
- Automotive repairs.
- Machinery maintenance.
- Professionals and enthusiasts encountering a broad range of fixings in their tasks.

General Specifications

Plier Type	Spanner Quick Grip
Number of Pieces	1
Overall Length	135 mm
Cutting Capacity	N/A
Material	Steel with PVC grips
ESD Safe	No
Jaw Width	9.65 mm
Jaw Opening	25 mm Max
Gripping Range	M1 (2.5 mm) – M12 (19 mm)
Non Sparking	No
Height Safe	No

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

