

Rexel A4 Polypropylene Lever Arch File

A4 Polypropylene lever arch file for with standard mechanism, ideal for everyday use at home or in the office. 75mm Spine width can hold up to 500 A4 sheets. Pack of 10.

Attributes

- Standard mechanism with cover lock to keep the binder closed and upright on shelf
- Polypropylene cover with a grey paper lining inside
- Replaceable spine pocket labels for easy identification of content
- Thumbhole and protected metal edges for easy handling and secure document storage
- 500 A4 sheet capacity (80 gsm)
- Pack of 10 (yellow)
- FSC® certified



Specifications

Number	2115719
Colour	yellow
Dimensions (W x H x D)	72 x 318 x 290 mm
For Format	A4
Spine Label	Replaceable
Capacity	500 sheet (80gsm)
Spine Width (mm)	75
Slotted Cover	yes
Reinforced Edges	yes
Thumb Hole	yes
Weight	450 g
Pallet quantity	300
EAN code	5028252623742