



Product number 1171250141
EAN 4007123684854

DESCRIPTION

- LED spotlight with super-bright Everlight SMD LEDs and flat design.
- User-friendly mounting due to external, waterproof spring-loaded clamp.
- Front cover made of safety glass.
- Solid, modern aluminium housing.
- Adjustable mounting bracket.

TECHNICAL DATA

Luminous flux	1150 lm	With motion detector	No
Power consumption	10 W	With socket outlet	No
Luminous efficacy	138 lm/W	Impact strength	IK08
Energy efficiency class		Protection class	I
Colour rendering index	80-89 (class 1B)	Degree of protection (IP)	IP65
Min.-Max. Nominal input voltage	220 V - 240 V	Basic colour	black

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.32 kg
Weight of product (without packaging)	0.27 kg	Dimension LxWxH (incl. packing)	6 cm x 11.7 cm x 9.5 cm
Dimension LxWxH (without packing)	5 cm x 11.5 cm x 8.5 cm		

SCOPE OF DELIVERY

LED Light JARO 1060