

Product information

18V BAND SAW PORTABLE



Satisfying the professional's needs

DPB181Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Battery Capacity	Up to 4.0Ah
Capacity (Round Pipe)	64 mm
Capacity (Square Pipe)	64x64 mm
Blade Length	835 mm
Blade Width	13 mm
Blade Speed	0 - 3.2 m/sec
Vibration K factor	1.5 m/sec ²
Vibration no load	2.5 m/sec ²
Net weight	3.7 kg



- LED Job light with pre-glow function.
- Easy to Grip handle with anti-slip elastomer surface
- Adjustable stopper plate convenient to cut pipes near wall, floor and ceiling
- Easy blade replacement by quick blade tension release/stretch with lever
- High cutting efficiency

Details correct as of: 17-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com