



Datasheet



ENGLISH

RS PRO Black Dual Lock 5m roll

Stock No: 217-6997



Technical Specifications:

Operating Temperature Range: -20°F (29°C) and up to 158°F (70°C)	Material of Construction: Polypropylene
Engaged Thickness ± 15% (without liner) : 0.067 inch	Backing Colour: Clear
Dynamic Tensile : 42.4 lbs./sq. inch (kN/²) Disengagement Strength	Adhesive: clear Acrylic
Shelf Life : 12 months from date of manufacture when stored in original package at 72°F (21°C) and 50% relative humidity.	Liner: Paper , Diecuttable
	Weight: 0.31 grams/1"² (25mm)

Features & Benefits:

replace conventional fasteners

such as, screws, clips, rivets, snaps and bolts in many applications where items need to be accessed or repositioned frequently. Dual Lock low profile reclosable fasteners consist of continuous strips of plastic backing, with tiny plastic mushroom shaped stems protruding up from the backing strip. When two pieces of Dual Lock low profile reclosable fasteners are pressed together, thousands of “mushroom heads” interlock with one another creating an audible snap which announces that the fastener is locked. The Dual Lock low profile reclosable fastener is thinner allowing it to be more flexible than similar reclosable fasteners.



rspro.com

