

TEROSON WX 180 POLISH

Known as Terotex Politurwachs September 2013

PRODUCT DESCRIPTION

TEROSON WX 180 POLISH provides the following product characteristics:

Application	Paint renovator
Technology	Solvent-based paint renovator and high-gloss polish
Basis	Hard Waxes

TEROSON WX 180 POLISH is a solvent-based paint renovator with a special combination of hard waxes (carnauba wax), high-gloss flow- and polishing agents. The material can be used after car wash by using a wet sponge.

APPLICATION AREAS

TEROSON WX 180 POLISH is especially useful for renovating the paintwork of used cars where the paint has suffered medium to severe weathering. TEROSON WX 180 POLISH cleans, polishes and protects car paintwork in one operation. It removes dirt which cannot be removed by thorough washing, it dissolves tar splashes, removes oil and insect residues and also removes small particles of surface rust.

TECHNICAL DATA

(Typical Test Results)

Colour	light blue
Odour	smells of wax and of petrol
Consistency	liquid
Density	approx. 0.93 g/cm ³
Solid	approx. 20 %
Viscosity	
(DIN 53211, 4 mm)	approx. 40 s
pH value	approx. 9.3
Application temperature	15 to 25 °C

PRELIMINARY STATEMENT

Prior to application it is necessary to read the **Material Safety Data Sheet** for information about precautionary measures and safety recommendations. Also, for chemical products exempt from compulsory labeling, the relevant precautions should always be observed.

Application

The vehicle is to be washed thoroughly before use and then dried. TEROSON WX 180 POLISH can also be applied directly onto the painted car body directly after car wash. Shake container well before use. Apply TEROSON WX 180 POLISH with a soft cloth or a damp sponge with gentle pressure in circular motions. After drying polish with cotton wool or cotton cloth. Do not process in direct sunlight or on hot car body.

STORAGE

Frost sensitive	no
Recommended storage temperature	10 to 20 °C
Shelf life	36 months

Disclaimer

Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.



TEROSON WX 180 POLISH

Known as Terotex Politurwachs September 2013

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Henkel AG & Co. KGaA

D-40191 Düsseldorf, Germany
Phone: +49-211-797-0
www.henkel.com

Henkel Central Eastern Europe GmbH

A-1030 Wien, Austria
Phone: +43-1711-040
www.henkel.com

Henkel & Cie AG

CH-4133 Pratteln, Switzerland
Phone: +41-61-825-7000
www.henkel.com

