



Adapter

432

Product no. **12030003**
GTIN **4018754012657**
Model **432**



Label. Adapter 3/8 "-1/2" L.31mm

Properties.

- 3/8 to 1/2"
- HPQ® high performance steel, chrome-plated
- DIN 3123 / ISO 3316

Technologies and features.



High Performance Quality (HPQ®)

Our HPQ® tool is made of wear-resistant high-performance steel, yet is thin-walled and lightweight. It withstands high torques and is ideal for work in confined spaces such as turbines.

Technical attributes.

External square drive (inch)	1/2
Internal square drive (inch)	3/8 "
d	17,2 mm
DIN	DIN 3123 / ISO 3316
Length mm (L)	31 mm
Alloy	Chrome Alloy Steel

Logistics data.

Depth mm (IFS)	32
Width mm (IFS)	18
Height mm (IFS)	18
WEEE/ElektroG	nicht ear-pflichtig
Length (packed, mm)	90
Width (packed, mm)	35
Height (packed, mm)	18
Volume (packed, dm3)	0.0567 dm3
Art. no.	12030003
Weight (gross, kg)	0,185

Weight PAP (kg)	0,000
Weight PVC (kg)	0,002
GTIN	4018754012657
Country of origin AWR	GERMANY
Region of origin	Nordrhein-Westfalen
Customs tariff no.	82042000
Packing standard	5
Weight	36 g

Variants.

Art. no.	Model no. (ERP)	Description	GTIN
12030003	432	Adapter 3/8 "-1/2" L.31mm	4018754012657

GTIN.



Accessories (for).



12261010
QR fine-tooth flexible
ratchet



12111030
QuickRelease ratchet,
fine tooth