

1504 0321

Mobile workbench

6 drawers

Code	ETIM
1814958	EC002224
EAN	UNSPSC
4010886856536	56-12-18-02
Country of origin	eCl@ss
Germany	21-10-02-00
Customs tariff number	
94032080	



Article description

- Drawers with one-hand operation and safety lock
- Load capacity per drawer 40 kg, lower heavy-duty drawer 60 kg
- Central locking with cylinder lock
- Static load capacity 1000 kg, in mobile operation 500 kg
- Dimensions: H 985 x B 1100 x T 630 mm

Article information

Contents (Qty of pieces)	1	Load capacity per drawer [kg]	40 kg
Version/Execution	Mobile workbench with 6 drawers	Drawer type	3x Type 1, H = 67 mm 2x Type 2, H = 137 mm 1x Type 3, H = 207 mm
Net weight [kg]	99 kg	Thickness (e.g. workplate)	30 mm
Total length [mm]	1.100 mm	Worktop dimensions	1100 x 550 x 30 mm
Total width [mm]	625 mm	Fixed roller diameter (2x)	200
Total height [mm]	990 mm	Swivel castor diameter with brakes (2x)	125
Surface	powder-coated	Single pull-out stop	no
Material	sheet steel	Number of shelves	1
Colour	GEDORE blue, RAL 5017	Number of wheels	4
Dimension (L x W x H)		Number of cabinets	1
Load capacity kg	750 kg	Working height	985
Number of crosswise dividers	2	Static load carrying capacity [kg]	1000 kg
Number of lengthwise dividers	3	Load capacity heavy duty drawer [kg]	60 kg
Number of drawers	6		