

Technical data sheet

Article number:
131-75019

RT250R

Product Group	Cable ties inside serrated with tuckaway
Product Family	RT250-Series up to 1115 N loop tensile strength
Material	Polyamide 6.6 (PA66)
Colour	Natural (NA)
Application Range	Indoor Use
Bundle Ø max.	125.0 mm
Bundle Ø min.	12.0 mm
Flammability	UL 94 V2
Length (L)	515.0 mm
Min.Tensile Strength	1115 N
Operating Temperature	-40 °C to +85 °C
Package Content packed in	pack
Pack Cont.	25 pcs.
Releasable Closure (Yes/No)	Yes
Specifications	UL-ZODZ2.E64139
Thickness (T)	1.9 mm
UL-File Number	E64139
Variant	Inside Serrated
Weight/Unit	0.0122 kg
Width (W)	12.5 mm

