


# MULTILINE LASER LEVEL 3x180°- GREEN BEAMS - USB-C

USB-C charging with built-in Li-ion batteries  
Li-ion batteries with POWERSTACK technology™  
Minimum autonomy of 8 hours  
USB-C cable charging: 80% charge in 30 minutes (45W PD)  
The laser can be used when loading



## VERY EFFICIENT

- High visibility diodes for a very clear visibility of the beams
- Accuracy +/- 3 mm at 10 m
- 30 M / 100 M with detection cell

## PRECISE

Fine alignment screw for simple and quick positioning of the beam on the user's markers

## PRACTICE

Indicator of the battery level to know if need recharge at a glance

## ADAPTS TO THE CONDITIONS OF THE SITE

With 3 light intensity adjustments of the beams to gain autonomy or to refine the beam according to the nature of the support material (stainless steel...)

## IS FIXED ANYWHERE

- Easy grip with very powerful swivel magnetic mount
- Built-in tripod thread of 1/4" and 5/8"

## VERSATILE

Button easy change of modes between manual slope / self-leveling / pendulum blocking

## RESISTANT

- Windows mounted on a rubber support seal
- IP65 (dust and low pressure water jet)
- Test fall 1 m
- Battery protected in the base in polycarbonate GF10 (very resistant and stable temperature and UV)



Delivered with compact soft case, wall bracket, USB-C cable.  
Plug not included

DCLE14301GB-XJ

5 035 048 810 804