




LOC	QTY	REV	DATE	APPD
G	14		2-24-93	18 DAP



<b>AMP</b> WIRE RANGE	<b>IL</b> E13288 Listed
26-22 AWG SOLID OR STRANDED	NOT LISTED
<b>LR7189</b> Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

- 1 STAMP AMP APPROX AS SHOWN
- 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS



<b>AMP INCORPORATED CUSTOMER SERVICE SYSTEMS</b>	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142
MAX RECOMMENDED OPERATING TEMPERATURE:	170°C MAX
VOLTAGE RATING:	NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE: SOLID OR STRANDED	0.1-0.41mm² [202-810] CIR MILS

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [ INCHES ] TOLERANCES ON: 2 PLG DEC ± 3 PLG DEC ± ANGLES ±	DR 2-24-93 TA BRINKMAN CHK 2-24-93 DA PATTERSON APPD 2-24-93 DE MILLER APPD 2-24-93 JI MECKLEY PRODUCT SPEC
MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254L [ .000100 ] MIN THK PER MIL-T-10727

DR 2-24-93 TA BRINKMAN	NAME
CHK 2-24-93 DA PATTERSON	<b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608
APPD 2-24-93 DE MILLER	SPLICE, BUTT, STRAP, SOLISTRAND™
APPD 2-24-93 JI MECKLEY	SIZE
PRODUCT SPEC	CAGE CODE
APPLICATION SPEC	DRAWING NO
WEIGHT	SCALE 10:1

100	LOOSE PIECE, BOX	8-321198-1
---	LOOSE PIECE	321198
QUANTITY	PACKAGE TYPE	PART NO

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-321198-1](#)